

TECHSPEC®

25.4mm H x 25.4mm L x 50mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#35-024** ☐ In Stock

- 1 +

C\$98.00

ADD TO CART

Qty 1-5
C\$98.00
Qty 6+
C\$78.40
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
50.00

Substrate: ☐
[N-BK7](#)

f/#:
1.96850393700787

Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 46.93
Center Thickness CT (mm): 4.65
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.4 x 25.4
Edge Thickness ET (mm): 1.31
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 25.84
Surface Quality: 60-40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View