

TECHSPEC® 25.4mm Kinematic Mount



25.4mm Kinematic Mount, #85-695

Stock **#85-695** **20+ In Stock**

- 1 + C\$274⁴⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$274.40 each
Need More?	Request Quote

Product Downloads

General

Tip-Tilt **Function:**

Circular **Type of Optics:**

Accepts 25/25.4mm Diameter Optics **Note:**

Physical & Mechanical Properties

30.0 **Compatible Plate Inner Diameter (mm):**

25.4	Inner Diameter (mm):
Black Anodized Aluminum	Construction:
12.7	Through Hole Diameter (mm):
30 Dia.	Dimensions (mm):
0.5	Adjustment Screw Pitch (mm):
±8 Tip/Tilt	Travel (°):

Threading & Mounting

25.0 - 25.4	Size of Compatible Optics (mm):
-------------	--

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Available for a Range of Optical Components
- Anodized Aluminum Construction with Stainless Steel Screws
- 0.5mm Pitch Fine Adjustment Screw
- [Fixed Optical Mounts](#) Also Available

Ideal for beam steering applications, TECHSPEC® Cage System Adjustable Optical Mounts are used to integrate a variety of optical components into a TECHSPEC Cage System. Designed to fit within the inner diameter of 25mm or 30mm standard [cage system plates](#), these optical mounts utilize set screws to secure optical components in place, providing the stability and adjustment needed for precision optical alignment. [#85-695](#) 25.4mm Kinematic Mount features a 12.7mm clear aperture and can be paired with [#85-699](#) 45° plate beamsplitter mount.