

25.4mm Travel, Metric Micrometer, Solid Top 44.4mm Stage



Stock **#55-461** ☒ In Stock

- 1 + **C\$1,517.60**

ADD TO CART

Qty 1+
C\$1,517.60

Volume Pricing
Request Quote

Get Product Downloads

Type of Movement: Linear (X)
Guide System: Ball Bearing
Type of Drive: Digital Micrometer (Metric)
Drive Orientation: Center Drive
Type: Metric

Stage Size (mm): 44.4 x 44.4
Travel (mm): 25
Construction: Aluminum Top and Base/440C Stainless Steel Bearings
Graduation (mm): 0.001
Load Capacity, Normal (kg): 11
Load Capacity, T_a (kg): 4.5
Load Capacity, T_b (kg): 2.3
Note: Solid Top
Stage Size (inches): 1.75 x 1.75
Straight Line Accuracy (µm): 2 per 25 mm of travel
Weight (g): 450

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View