

25° Diffusing Angle 25mm Dia Mounted



Stock **#54-498** CLEARANCE ☐ In Stock

-

1

+

C\$252.00

ADD TO CART

Qty 1-5
C\$252.00
Qty 6+
C\$214.20
Volume Pricing
Request Quote

Get Product Downloads

Angle Tolerance (°): ±2.5
Diffusing Angle (°): 25 (FWHM)
Clear Aperture CA (mm): 21.6
Diameter (mm): 25.00 ±0.1

Operating Temperature (°C): -30 to +100 (Maximum of 240 Hours)
Substrate: ☐ Polycarbonate
Thickness (mm): 2.60
Transmission (%): >85
Type: Holographic Diffuser
Wavelength Range (nm): 400 - 700
Construction: Mounted
Damage Threshold, By Design: ☐ 0.22 J/cm ² @ 1064nm, 10ns (typical)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant