

TECHSPEC® 25mm 1100-1620nm, 50R/50T, Non-Polarizing Cube Beamsplitter



Stock **#47-236** ☐ In Stock

1 **C\$396.20**

ADD TO CART

Qty 1-5
C\$396.20
Qty 6+
C\$310.80
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

Telecom
Coating Specification: R _{avg} <0.5% @ 1100 - 1620nm
Construction: Cube
Dimensions (mm): 25.0 x 25.0 x 25.0 ±0.1
Reflection/Transmission Ratio (R/T): 50/50
Substrate:  N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 1100 - 1620
[Ts-Tp]: <6%
Absolute Transmission (%): 45 ±10
Average Transmission (%): 45 ±5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View