

TECHSPEC® 25mm, 405 V-Coat, N-BK7 Laser Line RA Prism



Stock #83-201 CLEARANCE ☐ In Stock

-

1

+

C\$55.93

ADD TO CART

Qty 1+

C\$55.93

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Laser V-Coat (405nm)

Design Wavelength DWL (nm):
405

Substrate: ☐
[N-BK7](#)

Surface Quality:
40-20

Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 35.40
Length of Legs (mm): 25.00
Image Orientation: Left-Handed
Coating Specification: R _{abs} <0.25% @ 405nm
Ray Deviation (°): 90
Surface Flatness (P-V): λ/8

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View