

TECHSPEC[®] 25mm Cage 12.7mm Diameter Lens Mount



#85-545



Stock **#85-547** 20+ In Stock

-

1

+

C\$64^{.05}

ADD TO CART

Volume Pricing	
Qty 1+	C\$64.05 each
Need More?	Request Quote

Product Downloads

General	
Fixed	Function:
Circular	Type of Optics:
Fixed	Type:
Physical & Mechanical Properties	

25.0	Compatible Plate Inner Diameter (mm):
10.00	Length (mm):
11.00	Clear Aperture CA (mm):
Black Anodized Aluminum	Construction:

25 Dia.	Dimensions (mm):
---------	------------------

Threading & Mounting

12.7	Size of Compatible Optics (mm):
1.9 - 5.0	Thickness of Compatible Optics (mm):

M23.2 x0.75	Thread Type:
-------------	--------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:

Compliant	REACH 241:
-----------	------------

Product Details

- Available for a Range of Optical Lens Diameters
- Adds Additional Adaptability to Cage System
- Retaining Ring Included

TECHSPEC® Cage System Optical Lens Mounts, constructed of anodized aluminum, are designed to be used in a two-step process. First, secure the optical component within the lens mount using the included retaining ring. Second, secure the lens mount within the inner diameter of a [cage system plate](#). By enabling the addition and removal of lens mounts from plates, the system creates a wide range of flexibility for cage setups. TECHSPEC Cage System Optical Lens Mounts are ideal as stand-alone components or combined with [cage system tubes](#).

Note: [#85-678](#) is a two-piece assembly that can be used with either 25mm or 30mm cage system plates. Replacement retaining rings are sold separately.