

TECHSPEC® 25mm Dia 0.11 NA, Uncoated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock **#17-332** ☒ In Stock

[Other Coating Options](#)

1

C\$735.00

ADD TO CART

Qty 1-5

C\$735.00

Qty 6+

C\$588.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0/-0.025

Effective Focal Length EFL (mm):

100.00 @ 355nm
Numerical Aperture NA: 0.11
Back Focal Length BFL (mm): 96.30
Substrate: Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 355
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <1
Surface Quality: 40-20
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 3.85
Center Thickness CT (mm): 5.50 ±0.1
f/#: 4
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Power (diopters): 10.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View