

TECHSPEC®

25mm Dia., Protected Silver, $\lambda/10$ Stemmed Mirror



TECHSPEC® Stemmed Mirror



Stock **#14-582** ☒ In Stock

- 1 +

C\$214.20

ADD TO CART

Qty 1-5	C\$214.20
Qty 6+	C\$170.80
Volume Pricing	Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Surface Flatness (P-V):
 $\lambda/10$

Substrate: Fused Silica (Coming 7980)
Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture (%) : 90.00
Edges: Ground, protective bevel as needed
Thickness (mm): 13.00 ±0.20
Type: Stemmed Mirror
Wavelength Range (nm): 450 - 10000
Compatible Kinematic Mount: #58-853
Stem Diameter (mm): 12.50 +0.00/-0.10
Stem Length (mm): 6.50 ±0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View