

25mm Dia. x 10mm FL Protected Aluminum, Concave Mirror



Stock **#43-464** [CONTACT US](#)

[-](#) 1 [+](#)

C\$66.50

ADD TO CART

Qty 1-49
C\$66.50
Qty 50+
C\$56.70
Volume Pricing
Request Quote

Get Product Downloads

Substrate: [N-BK7](#)

Focal Length Tolerance (%):
±2

Surface Quality:
80-50

Diameter (mm):
25.00 ±0.50

Effective Focal Length EFL (mm): 10.00
Radius of Curvature (mm): 20.00
Aperture (f/#): f/0.4
Coating: Protected Aluminum (400-2000nm)
Coating Specification: R _{avg} >85% @400 - 700nm R _{avg} >90% @400 - 2000nm
Coating Type: Metal
Clear Aperture (%): 90
Edge Thickness ET (mm): 3.0
Radius R₁ (mm): 20.00
Thickness Tolerance (mm): ±0.5
Type: Spherical Mirror
Wavelength Range (nm): 400 - 2000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant