

TECHSPEC® 25mm Dia x 25mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #46-015 [CONTACT US](#)

-

1

+

C\$98.00

ADD TO CART

Qty 1-5

C\$98.00

Qty 6+

C\$78.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00

Effective Focal Length EFL (mm):
25.00

Substrate:

N-BK7

f/#:

1
Numerical Aperture NA: 0.5
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 17.74
Center Thickness CT (mm): 11.03
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.49
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.96
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View