

TECHSPEC®

25mm Dia. x 35mm FL, Uncoated Germanium Meniscus Lens



Stock **#87-957** ☐ In Stock

-

1

+

C\$560.00

ADD TO CART

Qty 1-5
C\$560.00
Qty 6+
C\$448.00
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
35.00

Substrate: ☐
Germanium (Ge)

f/#:
1.4

Numerical Aperture NA: 0.36
Coating: Uncoated
Type: Meniscus Lens
Wavelength Range (nm): 2000 - 14000
Back Focal Length BFL (mm): 33.29
Center Thickness CT (mm): 2.50
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <3
Clear Aperture (%) 90.00
Edge Thickness ET (mm): 1.6
Focal Length Specification Wavelength (µm): 10.6
Radius R₁ (mm): 38.43
Radius R₂ (mm): 57.61
Surface Quality: 60-40
Wavelength Range (µm): 2 - 14

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View