

TECHSPEC® 25mm Dia. x 40mm FL, Uncoated, Ge Plano-Convex Lens



Stock **#69-640** ☐ In Stock
[Other Coating Options](#)

-

1

+

C\$455.00

ADD TO CART

Qty 1-5
C\$455.00
Qty 6+
C\$364.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
40.00 @ 10.6µm

Back Focal Length BFL (mm):
39.25

Coating: Uncoated
Substrate: ☐ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.35
Radius R₁ (mm): 120.16
Clear Aperture CA (mm): 24
f#: 1.6
Numerical Aperture NA: 0.31
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 2000 - 14000

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View