

TECHSPEC®

25mm Dia. x 50mm FL Uncoated Calcium Fluoride PCX Lens



TECHSPEC Calcium Fluoride Plano-Convex (PCX) Lenses

Stock #88-164 ☒ In Stock



1



C\$259.00

ADD TO CART

Qty 1-5

C\$259.00

Qty 6+

C\$207.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
50.00 @266nm

Back Focal Length BFL (mm):
46.58

Coating: Uncoated
Substrate: ☐ Calcium Fluoride (CaF ₂)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/2
Centering (arcmin): <3
Center Thickness CT (mm): 5.00 ±0.1
Edge Thickness ET (mm): 1.33
Radius R₁ (mm): 23.11
Clear Aperture CA (mm): 22.5
f#: 2.00
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 7000
Axis Orientation: Random

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View