

**TECHSPEC® 25mm Dia. x 50mm FL, MgF<sub>2</sub> Coated, Plano-Convex Lens**



UV Fused Silica Plano-Convex (PCX) Lenses



Stock **#18-069** CLEARANCE ☐ In Stock

1

**C\$206.50**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| C\$206.50                     |
| Qty 6+                        |
| C\$165.20                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Diameter (mm):**  
25.00 -0.025

**Effective Focal Length EFL (mm):**  
50.00 @ 587.6nm

|                                                                                                    |
|----------------------------------------------------------------------------------------------------|
| <b>Back Focal Length BFL (mm):</b><br>46.00                                                        |
| <b>Coating:</b><br>MgF <sub>2</sub> (400-700nm)                                                    |
| <b>Coating Specification:</b><br>R <sub>avg</sub> ≤1.75% @ 400 - 700nm                             |
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">Fused Silica</a> (Corning 7980)          |
| <b>Surface Quality:</b><br>40-20                                                                   |
| <b>Power (P-V) @ 632.8nm:</b><br>3 Rings                                                           |
| <b>Irregularity (P-V) @ 632.8nm:</b><br>0.5 Rings                                                  |
| <b>Focal Length Tolerance (%):</b><br>±1                                                           |
| <b>Centering (arcmin):</b><br><1                                                                   |
| <b>Center Thickness CT (mm):</b><br>5.84 ±0.10                                                     |
| <b>Edge Thickness ET (mm):</b><br>2.13                                                             |
| <b>Radius R<sub>1</sub> (mm):</b><br>22.92                                                         |
| <b>Clear Aperture CA (mm):</b><br>24                                                               |
| <b>f/#:</b><br>2                                                                                   |
| <b>Numerical Aperture NA:</b><br>0.25                                                              |
| <b>Type:</b><br>Plano-Convex Lens                                                                  |
| <b>Bevel:</b><br>Protective bevel as needed                                                        |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                         |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>10 J/cm <sup>2</sup> @ 532nm, 10ns |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |