

TECHSPEC® 25mm Dia. x 75mm FL, 3 - 12µm Coated, Ge Plano-Convex Lens



Stock #87-948 ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$665.00

ADD TO CART

Qty 1-5

C\$665.00

Qty 6+

C\$532.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.1

Effective Focal Length EFL (mm):
75.00 @ 10.6µm

Back Focal Length BFL (mm):
75.25

Coating: BBAR (3000-12000nm)
Coating Specification: R _{avg} <5.0% @ 3 - 12µm
Substrate: ☐ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 2.65
Radius R₁ (mm): 225.29
Clear Aperture CA (mm): 24
f/#: 3.00
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 3000 - 12000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant