

TECHSPEC® 25mm Dia. x 75mm FL Uncoated Calcium Fluoride PCX Lens



TECHSPEC Calcium Fluoride Plano-Convex (PCX) Lenses

Stock **#88-165** ☐ In Stock

-

1

+

C\$259.00

ADD TO CART

Qty 1-5

C\$259.00

Qty 6+

C\$207.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
75.00 @266nm

Back Focal Length BFL (mm):
73.63

Coating: Uncoated
Substrate: ☐ Calcium Fluoride (CaF ₂)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: λ/2
Centering (arcmin): <3
Center Thickness CT (mm): 4.00 ±0.1
Edge Thickness ET (mm): 1.67
Radius R₁ (mm): 34.66
Clear Aperture CA (mm): 22.5
f#: 3.00
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 7000
Axis Orientation: Random

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View