

TECHSPEC®

25mm Dia. x 75mm FL, VIS-NIR, Inked, Double-Convex Lens



Stock **#45-891-INK** 3-5 DAYS

- 1 +

C\$84.00

ADD TO CART

Qty 1-9
C\$84.00
Qty 10+
C\$75.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.00

Back Focal Length BFL (mm):
73.84

Effective Focal Length EFL (mm): 75.00
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @ 400 - 870 nm R _{avg} ≤1.25% @ 890 - 1000nm
Substrate: 
Surface Quality: 40-20
Centering (arcmin): <1
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.10
Edge Thickness ET (mm): 1.45
Radius R₁=R₂ (mm): 76.66
Clear Aperture CA (mm): 24.00
f/#: 3.00
Focal Length Tolerance (%): ±1
Numerical Aperture NA: 0.17
Type: Double-Convex Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View