

TECHSPEC® 25mm Dia x -100mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#47-753** ☐ In Stock

1

C\$98.00

ADD TO CART

Qty 1-5

C\$98.00

Qty 6+

C\$78.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
-100.00

Substrate: ☐
[N-BK7](#)

f/#: 4.00
Numerical Aperture NA: 0.13
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -102.31
Center Thickness CT (mm): 3.50
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 5.03
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -51.68
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View