

25mm Diameter 0.04-1.5 OD, Circular ND Filter



Stock **#54-079** [CONTACT US](#)

- 1 + **C\$375.20**

ADD TO CART

Qty 1-9
C\$375.20
Qty 10+
C\$337.40
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
25.00

Angle of Incidence (°):
0.00

Optical Density OD (Average):
0.04 - 1.5

Substrate: ☐
[B270](#)

Inner Diameter (mm): 8.3
Coating: Variable
Thickness (mm): 2.00
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Parallelism (arcmin): 3.00
Optical Density Tolerance (%): ±8
Coating Specification: Continuously Variable Inconel from 0 - 310°

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View