

25mm Diameter, 0° AOI, Hot Mirror



Hot Mirrors

Stock **#43-842** ☐ In Stock

1

C\$64.40

ADD TO CART

Qty 1-9

C\$64.40

Qty 10+

C\$56.56

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):

0.00

Coating:

Hot Mirror, 0°

Diameter (mm):

25.00 ±0.25

Substrate: ☐

[BOROFLOAT®](#)

Reflection (%):
>95, 750 - 1150nm

Surface Quality:
80-50

Thickness (mm):
3.30

Transmission (%):
>90, 425 - 675nm

Type:
Shortpass Filter

Coating Specification:
Surface 1: 0° Hot Mirror
Surface 2: None

Wavelength Range (nm):
425 - 1150

Surface Flatness (P-V):
4 - 6λ

Coating Type:
Dielectric

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
