

25mm Diameter, 45° AOI, Hot Mirror



Hot Mirrors

Stock #43-955 ☒ In Stock



1



C\$64.40

ADD TO CART

Qty 1-9

C\$64.40

Qty 10+

C\$56.56

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):

45.00

Coating:

Hot Mirror, 45°

Diameter (mm):

25.00 ±0.25

Substrate:

[BOROFLOAT®](#)

Reflection (%):
>90, 750 - 1125nm

Surface Quality:
80-50

Thickness (mm):
3.30

Transmission (%):
>85, 425 - 675nm

Type:
Dichroic Filter

Coating Specification:
Surface 1: 45° Hot Mirror
Surface 2: None

Wavelength Range (nm):
425 - 1125

Surface Flatness (P-V):
4 - 6λ

Coating Type:
Dielectric

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)
