

TECHSPEC® 2.5mm Diameter, Fused Silica Ball Lens



Stock **#67-383** ☐ In Stock

-

1

+

C\$62.30

ADD TO CART

Qty 1-10
C\$62.30
Qty 11+
C\$49.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
2.50

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Coating:
Uncoated

Type:

Ball Lens
Wavelength Range (nm): 200 - 2200
Index of Refraction n_d: 1.458
Sphericity (μm): 0.625
Diameter Tolerance (μm): ± 2.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant