

TECHSPEC® 25mm Diameter x 150mm FL Uncoated, UV PCX Cylinder Lens



Stock #68-175 CLEARANCE ☐ In Stock

-

1

+

C\$153.93

ADD TO CART

Qty 1+

C\$153.93

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0.0/-0.2

Effective Focal Length EFL (mm):
150.00

Substrate: ☐
[Fused Silica](#) (Coming 7980)

f/#:
6.00

Numerical Aperture NA:
0.08

Coating: Uncoated	
Type: Cylinder Lens, Plano-Convex	
Wavelength Range (nm): 200 - 2200	
Back Focal Length BFL (mm): 147.94	
Center Thickness CT (mm): 3.00	
Center Thickness Tolerance (mm): ±0.1	
Edge Thickness ET (mm): 1.85	
Focal Length Tolerance (%): ±3	
Radius R (mm): 68.77	
Surface Quality: 40-20	
Wedge Tolerance (arcmin): 15.00	

Regulatory Compliance

RoHS: Compliant	
Certificate of Conformance: View	