

TECHSPEC® 25mm Diameter x 25mm FL, Uncoated, K22R Plastic Aspheric Lens



TECHSPEC® Plastic Aspheric Lenses

Stock **#21-206** ☐ **In Stock**

☐ [Other Coating Options](#)

1 **C\$68.60**

ADD TO CART

Qty 1-24

C\$68.60

Qty 25+

C\$49.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 +/-0.15

Effective Focal Length EFL (mm):
25.00 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 20.52
Substrate:  Zeonex K22R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Centering (arcmin): <5 (by design)
Surface Quality: 80-50
Clear Aperture CA (mm): 21.5
Edge Thickness ET (mm): 1.07
Center Thickness CT (mm): 7.40 ±0.20
f/#: 1.00
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to 70
Radius R₂ (mm): 152.34
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 350 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View