

TECHSPEC® 25mm Diameter x 40mm FL, Uncoated, Plastic Aspheric Lens



TECHSPEC® Plastic Aspheric Lenses

Stock **#66-010** CLEARANCE ☐ **In Stock**

[Other Coating Options](#)

1

C\$68.60

ADD TO CART

Qty 1-24

C\$68.60

Qty 25+

C\$49.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 +0.00/-0.10

Effective Focal Length EFL (mm):
40.00 @ 587.6nm

Numerical Aperture NA:
0.31

Back Focal Length BFL (mm): 37.09
Substrate:  Zeonex E48R
Aspheric Design Wavelength (nm): 587.6
Coating: Uncoated
Centering (arcmin): <5 (by design)
Surface Quality: 80-50
Clear Aperture CA (mm): 21.5
Edge Thickness ET (mm): 1.02
Center Thickness CT (mm): 4.80 ±0.20
f/#: 1.6
Bevel: Protective bevel as needed
Operating Temperature (°C): -30 to 70
Radius R₂ (mm): 269.8
Shape of Back Surface: Convex
Type: Aspheric Lens
Wavelength Range (nm): 350 - 1100
Conjugate Distance: Infinite

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View