

## 25mm FL SWIR Series Fixed Focal Length Lens



Stock **#68-688** ☐ In Stock

[Similar Products](#)

1

C\$2,947.00

ADD TO CART

|             |
|-------------|
| Qty 1+      |
| C\$2,947.00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|

Field of View @ Min Working Distance (mm):  
150.00

Iris Option:  
Variable

Length (mm):  
43.00 - 48.4

Filter Thread:  
M35.5 x 0.5

Maximum Diameter (mm):  
43

|                                                      |
|------------------------------------------------------|
| <b>Weight (g):</b><br>135                            |
| <b>Horizontal Field of View, 1" Sensor:</b><br>29.3° |
| <b>Maximum Image Circle (mm):</b><br>16.00           |
| <b>Type:</b><br>Fixed Focal Length Lens              |
| <b>Focal Length FL (mm):</b><br>25.00                |
| <b>Maximum Sensor Format:</b><br>1"                  |
| <b>Working Distance (mm):</b><br>300 - ∞             |
| <b>Mount:</b><br>C-Mount                             |
| <b>Aperture (f/#):</b><br>f/1.4 - f/16               |
| <b>Distortion (%):</b><br><-1.0                      |
| <b>Lens Wavelength Range:</b><br>SWIR                |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Exempt</a>                |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 240:</b><br><a href="#">Contains SVHC(s)</a>      |