

TECHSPEC[®] 25mm H x 50mm L x 25mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#46-020** ☐ In Stock

-

1

+

C\$154.00

ADD TO CART

Qty 1-5
C\$154.00
Qty 6+
C\$123.20
Volume Pricing
Request Quote

Get Product Downloads



Effective Focal Length EFL (mm):
25.00

Substrate: ☐
[N-BK7](#)

f/#:
1

Numerical Aperture NA:

0.5
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 17.74
Center Thickness CT (mm): 11.03
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 1.49
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 12.96
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View