



25mm H x 50mm L x -75mm FL VIS 0° Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#69-808** ☐ In Stock

1 **C\$177.80**

ADD TO CART

Qty 1-5

C\$177.80

Qty 6+

C\$142.10

Volume Pricing

[Request Quote](#)

Get Product Downloads



Effective Focal Length EFL (mm):
-75.00

Substrate: ☐
[N-BK7](#)

Coating:
VIS 0° (425-675nm)

Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): -77.64
Center Thickness CT (mm): 4.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 25.0 x 50.0
Edge Thickness ET (mm): 5.97
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -38.76
Surface Quality: 60-40
Damage Threshold, Reference: ☐ 5 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant