

TECHSPEC 25mm Length, C-Mount Extension Tube



Stock #58-736 **20+ In Stock**

⊖ 1 ⊕ C\$61.60

ADD TO CART

Volume Pricing

Qty 1-4	C\$61.60 each
Qty 5-9	C\$55.02 each
Qty 10-25	C\$51.10 each
Need More?	Request Quote

Product Downloads

General

Extension Tube **Type:**

Extension Tube (Fixed) **Function:**

Physical & Mechanical Properties

25.0 **Extension Length (mm):**

Total Length (mm):
29.0

Clear Aperture CA (mm):
22.0

Outer Diameter (mm):
30.0

Threading & Mounting

Thread Type:
C-Mount

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Compliant](#)

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

