

TECHSPEC® 25mm N-BK7 Wedged Window

See More by [SCHOTT Optical Components](#)



Stock #34-245 [CONTACT US](#)

⊖ 1 ⊕

C\$168.00

ADD TO CART

Qty 1-5

C\$168.00

Qty 6+

C\$134.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
22.50

Diameter (mm):
25.00 +0.0/-0.10

Thickness (mm):
3.00 ±0.20

Coating:
Uncoated

Coefficient of Thermal Expansion CTE ($10^{-6}/^{\circ}\text{C}$):
7.1 (-30 to +70°C)
8.3 (+20 to +300°C)

Edges:
Fine Ground

Index of Refraction n_d :
1.516

Substrate:
[N-BK7](#)

Surface Flatness (P-V):
λ/10 over 25mm Aperture

Surface Quality:
20-10

Type:
Wedged Window

Wavelength Range (nm):
350 - 2200

Young's Modulus (GPa):
82

Wedge Angle:
30' ±10'

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 240:
[Compliant](#)
