

25mm Outer Dia., Zero Aperture, Burnished Steel Leaves



Zero Series

Stock **#57-587** ☐ In Stock

-

1

+

C\$137.20

ADD TO CART

Qty 1-4

C\$137.20

Qty 5+

C\$120.96

Volume Pricing

[Request Quote](#)

Get Product Downloads

Minimum Aperture (mm):
0.00

Maximum Aperture (mm):
12.0

Outer Diameter (mm):
25.0

Construction:

Anodized Aluminum Alloy, Burnished Leaves
Full Angular Range of Lever (°): 96.00
Lever Diameter (mm): 3.00
Lever Length (mm): 12.00
Lever Position (mm): 2.50
Number of Leaves: Two sets of 6
Operating Temperature (°C): <250
Pin Thread & Pitch: M1.4 x0.30mm
Thickness (mm): 5.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant