

25mm Travel, Metric Micrometer, Solid-Top Ball Bearing Stage



32mm/1.25" Center drive stage and its X-Y-Z configuration



Stock **#13-772** ☐ In Stock

1

C\$1,195.60

ADD TO CART

Qty 1+
C\$1,195.60

Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Metric Micrometer

Drive Orientation:
Center Drive

Type: Metric
Stage Size (mm): 127 x 127
Travel (mm): 25
Construction: Aluminium Stage
Graduation (mm): 0.01
Height (mm): 25.4
Load Capacity, Normal (kg): 48
Load Capacity, T_a (kg): 13.6
Note: Solid Top
Straight Line Accuracy (µm): 2 per 25mm of travel
Weight (kg): 1.2
Thrust Capacity, T_a (kg): 13.6
Thrust Capacity, T_b (kg): 1.1

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View