

25mm Ultra Broadband Wire Grid Linear Polarizer



Mounted Ultra Broadband Wire Grid Linear Polarizer

Stock **#34-315** [CONTACT US](#)

⊖ 1 ⊕

C\$1,855.00

ADD TO CART

Qty 1-10
C\$1,855.00
Qty 11+
C\$1,596.00
Volume Pricing
Request Quote

Get Product Downloads

Angle of Incidence (°):
±20 without depolarization

Clear Aperture CA (mm):
19.0

Diameter (mm):
25.00

Extinction Ratio:

5000:1 @ 3200nm
Substrate: Fused Silica (Coming 7980)
Operating Temperature (°C): -40 to +200
Surface Quality: 80-50
Thickness (mm): 5.80
Transmission (%): >80 (Typical) @ 450nm
Type: Linear Polarizer
Dimensional Tolerance (mm): ±0.4
Construction: Wire Grid
Thermal Expansion: 5.5 x 10 ⁻⁷ /°C
Alignment Tolerance (°): ±1.0
Wavelength Range (nm): 300 - 3200

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View