

TECHSPEC® 25mm, Uncoated, Fused Silica, Right Angle Prism



TECHSPEC UV Fused Silica Right Angle Prisms

Stock **#47-786** [CONTACT US](#)

- 1 +

C\$148.40

ADD TO CART

Qty 1-5

C\$148.40

Qty 6+

C\$119.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[Fused Silica](#) (Coming 7980)

Surface Quality:

60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.10 Legs
Angle Tolerance (arcmin): ±5
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 35.40
Length of Legs (mm): 25.00
Pyramid Tolerance (arcmin): ±5
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/2
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
