

TECHSPEC® 25mm, Uncoated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock **#32-336** ☐ **In Stock**

-

1

+

C\$98.00

ADD TO CART

Qty 1-5

C\$98.00

Qty 6+

C\$88.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

[N-BK7](#)

Surface Quality:

60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 35.40
Length of Legs (mm): 25.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View