

TECHSPEC® 25mm VIS, 50R/50T, Non-Polarizing In-Line Cube Beamsplitter



Stock **#20-096** ☐ In Stock

-

1

+

C\$406.00

ADD TO CART

Qty 1-5

C\$406.00

Qty 6+

C\$348.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating:

MS
Coating Specification: R _{avg} <0.5% @ 430 - 670nm
Construction: Cube
Dimensions (mm): 25.0 x 25.0 x 25.0
Note: Absorptive Surface Treatment on Blackened Face
Reflection/Transmission Ratio (R/T): 50/50
Substrate: ☐ N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 430 - 670
[Ts-Tp]: <6%
Absolute Transmission (%) 45 ±10
Average Transmission (%) 45 ±5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View