

**TECHSPEC® 25mm VIS, 50R/50T, Non-Polarizing Cube Beamsplitter**



Stock **#47-009** ☐ In Stock

- 1 + **C\$396.20**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| C\$396.20                     |
| Qty 6+                        |
| C\$310.80                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Beam Deviation (arcmin):**  
≤2

**Bevel:**  
Protective bevel as needed

**Clear Aperture (%):**  
>90

**Coating:**

|                                                                                                                              |
|------------------------------------------------------------------------------------------------------------------------------|
| MS                                                                                                                           |
| <b>Coating Specification:</b><br>R <sub>avg</sub> <0.5% @ 430 - 670nm                                                        |
| <b>Construction:</b><br>Cube                                                                                                 |
| <b>Dimensions (mm):</b><br>25.0 x 25.0 x 25.0 ±0.1                                                                           |
| <b>Reflection/Transmission Ratio (R/T):</b><br>50/50                                                                         |
| <b>Substrate:</b> <br><a href="#">N-BK7</a> |
| <b>Surface Flatness (P-V):</b><br>λ/8                                                                                        |
| <b>Surface Quality:</b><br>40-20                                                                                             |
| <b>Type:</b><br>Non-Polarizing Beamsplitter                                                                                  |
| <b>Wavelength Range (nm):</b><br>430 - 670                                                                                   |
| <b>[Ts-Tp]:</b><br><6%                                                                                                       |
| <b>Absolute Transmission (%):</b><br>45 ±10                                                                                  |
| <b>Average Transmission (%):</b><br>45 ±5                                                                                    |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---