

25mm x 25mm 220 Grit Ground Glass Diffuser



Stock **#45-654** ☐ In Stock

- 1 +

C\$28.70

ADD TO CART

Qty 1-10
C\$28.70
Qty 11+
C\$25.20
Volume Pricing
Request Quote

Get Product Downloads

Coating:
Uncoated

Dimensional Tolerance (mm):
±0.76

Dimensions (mm):
25.00 x 25.00

Edges:
Cut Edges

Grit: 220
Substrate: Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 25.00
Note: Sandblasted on first surface
Length (mm): 25.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant