

25µm Aperture Diameter, Mounted, Precision Pinhole



25µm Aperture Diameter, Mounted, Precision Pinhole, #56-280

Stock **#56-280** ☐ In Stock



1



C\$105.00

ADD TO CART

Qty 1-5

C\$105.00

Qty 6+

C\$92.68

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type:
Mounted

Outer Diameter (mm):
25 +0.4/-0.000

Construction:
Stainless Steel

Fixed Aperture Diameter (µm):

25
Thickness (mm): 0.01 Nominal
Aperture Tolerance (µm): ±5
Mount Thickness (mm): 1.25 ±0.05
Aperture Centration (µm): ±125

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

