


27mm Diameter, White Ivory Glass Index Grid Reticle Target



27mm Diameter, White Ivory Glass Index Grid Reticle Target, #58-772



Stock **#58-772** ☐ In Stock

-

1

+

C\$312.20

ADD TO CART

Qty 1-4
C\$312.20
Qty 5+
C\$297.92
Volume Pricing
Request Quote

Get Product Downloads

Coating:

Low Reflection Chromium First Surface

Diameter (mm):

27.00 ±0.050

Substrate:

White Ivory Soda Lime Glass
Line Width (mm): 0.0254 ±0.0025
Optical Density OD (Average): OD > 3.0
Pattern Size (mm): 10
Surface Quality: 40-20
Thickness (inches): 1/8
Thickness (mm): 3.20
Edges: Smoothed for Safe Handling
Accuracy (mm): 0.001
Surface Flatness (P-V): 1λ
Reflection (%): < 5% @ 550nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View