

2.9mm FL, No IR-Cut Filter, f/2, Micro Video Lens



Stock #55-570 CLEARANCE ☒ In Stock

-

1

+

C\$55.93

ADD TO CART

Qty 1+

C\$55.93

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
17.40

Filter Thread:
M12 x0.50

Maximum Diameter (mm):
15.0

Maximum Image Circle (mm):
6.00

Horizontal Field of View @ Max Sensor Format:
98.6

Resolution, On-Axis: 63 lp/mm @ 20% Contrast
Resolution, 0.7 Field: 63 lp/mm @ 20% Contrast
Resolution, Full Field: 40 lp/mm @ 20% Contrast
Note: Standard
Type: M12 Imaging Lens
Focal Length FL (mm): 2.90
Maximum Sensor Format: 1/3"
Working Distance (mm): 400 - ∞
Mount: M12 x 0.5 (S-Mbunt)
Aperture (f/#): f/2
Distortion (%): -36.0 @ Full Field
IR Cut Filter: No
Lens Wavelength Range: VS

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View