

2° Commercial Grade Wedge Prism



Stock #27-677 CLEARANCE ☐ In Stock

- 1 +

C\$34.93

ADD TO CART

Qty 1+
C\$34.93

Volume Pricing
Request Quote

Get Product Downloads

Coating:
MgF₂ (400-700nm)

Angle Tolerance (arcmin):
1.00

Coating Specification:
R_{avg} ≤1.75% @ 400 - 700nm

Diameter (mm):
25.00 ±0.1

Image Orientation:
Beam Deviation

Power (diopters): 3.49
Substrate: N-BK7
Surface Accuracy: 1λ
Thickness (mm): 3.00
Type: Wedge Prism
Wedge Angle: 3° 52'0"
Wedge Angle Deviation (°): 2.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View