

## 2° Diffusing Angle 25mm Dia., Fused Silica Holographic Diffuser



Holographic UV Diffusers

Stock **#35-693** ☐ In Stock



1



C\$640.50

ADD TO CART

Qty 1+

C\$640.50

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (°):  
±1

Diffusing Angle (°):  
2 (FWHM)

Clear Aperture CA (mm):  
21.6 ±0.1

Diameter (mm):  
25.00 ±0.1

Operating Temperature (°C):  
-40 to +170

Substrate:   
[Fused Silica](#) (Corning 7980)

Transmission (%):  
Typical: 90

Type:  
Holographic Diffuser

Wavelength Range (nm):  
400 - 700

Construction:  
Mounted

Mount Thickness (mm):  
4.7 ±0.1

Regulatory Compliance

RoHS 2015:  
[Compliant](#)

Certificate of Conformance:  
[View](#)

Reach 233:  
[Compliant](#)