

## 2" x 2" (10 lp/mm), Ronchi Ruling



Stock **#58-783** **1 In Stock**

⊖ 1 ⊕ C\$371<sup>00</sup>

**ADD TO CART**

### Volume Pricing

|            |                               |
|------------|-------------------------------|
| Qty 1-4    | C\$371.00 each                |
| Qty 5+     | C\$353.08 each                |
| Need More? | <a href="#">Request Quote</a> |

### Product Downloads

### General

Metric **Type:**

### Physical & Mechanical Properties

**Dimensional Tolerance (inches):**  
±0.02

**Dimensions (inches):**  
2 x 2

**Thickness (mm):**  
1.50

± 0.02      **Dimensional Tolerance (mm):**

≤2      **Line to Line Parallelism (arcsec):**

±1      **Parallelism of Pattern to Substrate (°):**

## Optical Properties

Vacuum Deposited Chrome, OD >3.0      **Coating:**

10      **Frequency (lp/mm):**

Float Glass      **Substrate:** □

3.00      **Optical Density OD (Average):**

20-10      **Surface Quality:**

1λ      **Surface Flatness (P-V):**

## Regulatory Compliance

[Compliant](#)      **RoHS 2015:**

[View](#)      **Certificate of Conformance:**

[Compliant](#)      **Reach 240:**

## Product Details

- Chrome on Glass
- High Tolerance
- Superior to Etched and Filled Rulings
- Lines Parallel to Edge
- English and Metric Versions Available

High Precision Ronchi Rulings are excellent for evaluating resolution, field distortion, and parfocal stability. The glass targets are coated with vacuum-deposited chrome and have a float glass substrate. English and Metric version are available with various Linepairs Per Inch (LPI) and Linepairs Per Millimeter (lp/mm) measurements. High Precision Ronchi Rulings are offered in 0.5", 1", 2", and 4" squares.