

2" x 2" (300 lp/inch), Ronchi Ruling



Stock **#56-610** ☐ In Stock

1

C\$431.20

ADD TO CART

Qty 1-4

C\$431.20

Qty 5+

C\$409.78

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Substrate:
Float Glass

Optical Density OD (Average):
3.00

Dimensions (inches): 2 x2
Surface Quality: 60-40
Thickness (mm): 1.50
Type: English
Parallelism (arcmin): ±60
Dimensional Tolerance (mm): ± 0.02
Frequency (lp/inch): 300.00
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
