

2" x 2" Red Advanced Illumination Side-Fired Backlight

See More by [Advanced Illumination](#)



Stock **#88-503** [CONTACT US](#)

- 1 + **C\$800.80**

ADD TO CART

Qty 1+
C\$800.80

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: Red
Model Number: BX0202-625-IC
Operating Temperature (°C): 0 to 60
Dimensions (mm): 115.1 L x 115.1 W x 20.1 D

Wavelength (nm): 625.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of Channels: 1.00
Active Area (inches): 2 x2
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)