

30°, 405nm Single Line Projection Head



30°, 405nm Single Line Projection Head

Stock **#37-092** ☐ In Stock



1



C\$185.50

ADD TO CART

Qty 1-9

C\$185.50

Qty 10+

C\$166.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Outer Diameter (mm):
12.00

Type:
Laser Accessory

Power Supply:
Power Supply Required and Sold Separately.
USA: [#83-855](#)
Europe: [#83-855](#)

Japan: [#13-640](#)
Korea: [#33-770](#)
China: [#83-855](#)

Fan Angle (°):
30.00

Length (mm):
4.00

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)