

Coherent® StingRay™ Projection Head 1254118 | 514nm, 30° Fan

See More by [Coherent®](#)



30° Line, 514nm Stingray Projection Head, #89-574

Stock **#89-574** 1 In Stock

-

1

+

C\$540^{.40}

ADD TO CART

Volume Pricing	
Qty 1+	C\$540.40 each
Need More?	Request Quote

Product Downloads



General

1 Line

Type:

[86-848, 87-522](#)

Compatible Laser Models:

Coherent®

Manufacturer:

Optical Properties

514.00

Wavelength (nm):

Green	Color:
30.00	Fan Angle (°):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- External Focus with up to 100mW Output Power
- Auto Scaling Input Power 5 - 24VDC with Reverse Polarity Protection
- Built-In Microcontroller for Fault Monitor
- [Coherent® StingRay™ Developer's Kit](#) also available

Coherent® StingRay™ and BioRay™ Laser Diode Modules are ideal for a variety of alignment, machine vision, and biomedical applications. They are available in a wide range of output powers, wavelengths, and fan angles. High precision optical components and sophisticated drive electronics provide power and control to your application, reducing signal-to-noise ratios and increasing measurement speed. Coherent® StingRay™ and BioRay™ Laser Diode Modules are designed with a flat top power distribution across the beam profile for consistency in line projection widths.

Note: For CDRH certified systems (Class IIIb), [#86-878](#) Laser Controller and additional external voltage source (0.5–5V) with BNC connector is required.