

3.0 OD M30.5 x 0.50, Machine Vision Absorptive ND Filter



Stock #21-772

CONTACT US

-

1

+

C\$148.40

ADD TO CART

Qty 1-9
C\$148.40
Qty 10+
C\$142.52
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
3.0

Clear Aperture CA (mm):
25.50

Filter Thread:
M30.5 x 0.50

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 0.10
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
